


Patient Chair 1395

Overall Dimensions	23.5"w x 25"d x 45"h	COM 54"	2.25 yds.
Seat Dimensions	21.25"w x 18.5"d x 18.5"h	Shipping Weight	41 lbs.
Seat to Top of Back	24"	Cubic Feet	27
Top of Arm to Floor	25.5	Exposed Metal	Luster Grey Powder Coat



Standard Features	Options Available
<ul style="list-style-type: none"> • 3/4" Tubular Bent Luster Grey Powder Coated Metal Frame • Black Resin Arm Cap • European Beech Wood Arm Cap is Optional • Upholstered Seat and Back • Spring Seat Construction • Clean-Thru Design • Wall-Saver Design • Tight Cushion • White Plastic Glide Fitted into the Bottom of Tubular Leg • Field Replaceable Components 	<ul style="list-style-type: none"> • Wood Arm Caps • Removable Seat and Back Covers • Multiple Fabric Applications • CAL 133 TB Certified • Moisture Barrier

Standard Textile & Finish Selection

<http://carolina.ofs.com/resources/textiles>
<http://carolina.ofs.com/resources/finishes>

Frame Construction

Seat	<ul style="list-style-type: none"> • 3/4" plywood seat frame panel with seat springs spanning the openings in the plywood frame • Topped with contour cut foam
Back	<ul style="list-style-type: none"> • 3/4" plywood assembled back frame (chair and loveseat) is covered with a stretch webbing and foam is applied to the face
Arms	<ul style="list-style-type: none"> • Upholstered Arms: 1 3/4" wide x 1 1/2" thick molded plywood frame that fits halfway over a metal 3/4" (13 gauge) diameter bent tube frame exposing 1/2 of the powder coated tubular leg • Wood Arms: 1 3/4" wide x 1 1/2" thick molded European Beech frame that fits halfway over a metal 3/4" (13 gauge) diameter bent tube frame exposing 1/2 of the powder coated tubular leg • Resin Arms: 3/6" black resin arm cap that attaches to the arm via machine screws from underneath
Assembly	<ul style="list-style-type: none"> • Seat: Attached to a 3/4" x 3/4" (16 gauge) powder coated tube frame via 1/4" - 20 connector bolts • Back: 1/4" thick powder coated metal back brackets attached to the wood frame underneath the foam • The brackets and back assembly are then attached to the 3/4" x 3/4" powder coated tube frame via 1/4" - 20 connector bolts underneath the seat

Foam

Seat/Back	<ul style="list-style-type: none"> • Premium Grade Foam • CAL TB 117 Certified Fire Retardant
-----------	---