

Meeting Room planning guide






Table of contents

Base compatibility	3-8
Power cutout locations	9-10
Power and base compatibility	11-12


Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.

BASE OPTIONS FOR ROUND AND SQUARE TOPS




NOTE: All round and square conference tops require additional weight in the base when using cylinder bases to prevent the table from tipping over. OFS provides instruction sheets and clear 6 ml bags with base. Customer must provide dry sand for the additional weight.

36"D TOPS




42"D AND 48"D TOPS




Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.

BASE OPTIONS FOR ROUND AND SQUARE TOPS




NOTE: All round and square conference tops require additional weight in the base when using cylinder bases to prevent the table from tipping over. OFS provides instruction sheets and clear 6 ml bags with base. Customer must provide dry sand for the additional weight.


54"D AND 59 1/2"D TOPS




CBU-F




CBU-M




CBU-Q



CBU-R



CBU-04



CBU-06




MLX-1



MLC-1

Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.


BASE OPTIONS FOR RECTANGULAR, BOAT-SHAPED AND RACETRACK TOPS (BASES INSET 20")




72"W X 36"D TOPS




CBD-B (2 Qty.)
26" Between Bases




CBD-S (2 Qty.)
35.75" Between Bases




CBD-U (2 Qty.)
35.4375" Between Bases



CBD-Y (2 Qty.)
36.75" Between Bases




CBD-12 (2 Qty.)
27" Between Bases




MCB-23 (2 Qty.)
(For Rectangular and Racetrack Tops)
13" Between Bases


96"W X 42"D TOPS




CB-A (2 Qty.)
34.9375" Between Bases



CB-B (2 Qty.)
30.5" Between Bases




CB-C (2 Qty.)
34.375" Between Bases




CB-D (2 Qty.)
44.3125" Between Bases




CB-24EB (2 Qty.)
41.25" Between Bases




CB-S (2 Qty.)
43.75" Between Bases



CB-U (2 Qty.)
43.4375" Between Bases




CB-2V (2 Qty.)
48.5625" Between Bases




CB-Y (2 Qty.)
44.75" Between Bases




CB-03 (2 Qty.)
35" Between Bases




CBH-03 (2 Qty.)
25" Between Bases




CB-05 (2 Qty.)
33.25" Between Bases



CBH-05 (2 Qty.)
23.25" Between Bases




CB-12 (2 Qty.)
35" Between Bases




MCB-23 (2 Qty.)
21" Between Bases

Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.

BASE OPTIONS FOR RECTANGULAR, BOAT-SHAPED AND RACETRACK TOPS (BASES INSET 20")




120"W X 48"D AND 144"W X 48"D TOPS




CB-A (2 Qty.) + CB-D Base
28" Between Bases (120)
40" Between Bases (144)




CB-B (2 Qty.) + CB-Y Base
26" Between Bases (120)
38" Between Bases (144)




CB-C (2 Qty.) + CB-D Base
27.75" Between Bases (120)
39.75" Between Bases (144)




CB-D (3 Qty.)
32.6875" Between Bases (120)
44.6875" Between Bases (144)




CB-24EB (3 Qty.)
29.625" Between Bases (120)
41.625" Between Bases (144)




CB-S (3 Qty.)
32.125" Between Bases (120)
44.125" Between Bases (144)



CB-U (3 Qty.)
31.8125" Between Bases (120)
43.8125" Between Bases (144)



CB-2V (2 Qty.) + CB-U Base
34.375" Between Bases (120)
46.375" Between Bases (144)




CB-Y (3 Qty.)
33.125" Between Bases (120)
45.125" Between Bases (144)




CB-03 (3 Qty.)
25.5" Between Bases (120)
37.5" Between Bases (144)




CB-03 (2 Qty.) + CBH-03 Base
21" Between Bases (120)
33" Between Bases (144)




CB-05 (3 Qty.)
23.75" Between Bases (120)
35.75" Between Bases (144)



CB-05 (2 Qty.) + CBH-05 Base
19.25" Between Bases (120)
31.25" Between Bases (144)




CB-12 (3 Qty.)
25.5" Between Bases (120)
37.5" Between Bases (144)



MCB-28 (3 Qty.)
6" Between Bases (120)
18" Between Bases (144)


120"W X 48"D TOPS ONLY




CB-B (2 Qty.) + CBH-F Base
17.3125" Between Bases (120)




CB-B (2 Qty.) + CBU-F Base
29.25" Between Bases (144)




CBH-03 (3 Qty.)
24" Between Bases (144)



CBH-05 (3 Qty.)
22.25" Between Bases (144)




CB-05BK8027




CB-05BK10427

Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.


BASE OPTIONS FOR RECTANGULAR, BOAT-SHAPED AND RACETRACK TOPS (BASES INSET 20")




168"W X 48"D TOPS




CB-A (2 Qty.) +
CB-D Base
52" Between Bases




CB-B (2 Qty.) +
CBH-F Base
41.25" Between Bases



CB-B (2 Qty.) +
CB-Y Base
50" Between Bases




CB-C (2 Qty.) +
CB-D Base
51.75" Between Bases




CB-D (3 Qty.)
56.6875" Between Bases




CB-24EB (3 Qty.)
53.625" Between Bases



CBH-F (3 Qty.)
32.125" Between Bases




CB-M (3 Qty.)
33" Between Bases




CB-Q (3 Qty.)
34.5625" Between Bases




CB-R (3 Qty.)
29.875" Between Bases




CB-S (3 Qty.)
56.125" Between Bases



CB-U (3 Qty.)
55.8125" Between Bases



CB-2V (2 Qty.) +
CB-U Base
58.375" Between Bases




CB-Y (3 Qty.)
57.125" Between Bases




CB-03 (3 Qty.)
49.5" Between Bases




CB-03 (2 Qty.) +
CBH-03 Base
45" Between Bases




CBH-03 (3 Qty.)
36" Between Bases




CBH-04 (3 Qty.)
27.5" Between Bases




CB-05 (3 Qty.)
47.75" Between Bases




CB-05 (2 Qty.) +
CBH-05 Base
43.25" Between Bases




CBH-05 (3 Qty.)
34.25" Between Bases




CBH-06 (3 Qty.)
25.75" Between Bases



CB-12 (3 Qty.)
49.5" Between Bases




MCB-28 (3 Qty.)
30" Between Bases




CB-05BK12827

Our conference offering includes numerous base choices to complement our tops. For easy selection of bases we have compiled this quick reference guide of compatible bases with tops.


BASE OPTIONS FOR RECTANGULAR, BOAT-SHAPED AND RACETRACK TOPS (BASES INSET 20")




192"W X 48"D TOPS




CB-A (2 Qty.) +
CB-D Base (2 Qty.)
41" Between Bases




CB-B (2 Qty.) +
CB-Y Base (Qty.)
40" Between Bases



CB-C (2 Qty.) +
CB-D Base (2 Qty.)
41" Between Bases




CB-D (4 Qty.)
44.75" Between Bases



CB-24EB (4 Qty.)
41.75" Between Bases




CBH-F (3 Qty.)
44.125" Between Bases




CBU-F (3 Qty.)
37.375" Between Bases




CB-M (3 Qty.)
45" Between Bases




CBU-M (3 Qty.)
37.5" Between Bases




CB-Q (3 Qty.)
46.5625" Between Bases




CB-R (3 Qty.)
41.875" Between Bases




CBU-R (3 Qty.)
35.25" Between Bases




CB-S (4 Qty.)
44.25" Between Bases



CB-U (4 Qty.)
44" Between Bases



CB-2V (2 Qty.) +
CB-U Base (2 Qty.)
45.25" Between Bases



CB-Y (4 Qty.)
45.25" Between Bases



CB-03 (4 Qty.)
38.375" Between Bases




CBH-03 (3 Qty.)
48" Between Bases




CBH-04 (3 Qty.)
39.5" Between Bases




CBU-04 (3 Qty.)
37.5" Between Bases




CB-05 (4 Qty.)
37.5" Between Bases




CBH-05 (3 Qty.)
46.25" Between Bases




CBH-06 (3 Qty.)
37.75" Between Bases




CBU-06 (3 Qty.)
34.75" Between Bases



CB-12 (4 Qty.)
38.375" Between Base:



MCB-28 (3 Qty.)
42" Between Bases



CB-05BK15227



Meeting Room planning guide

POWER CUTOUT LOCATIONS

To order, add location code(s) to model number.


Example: CT5-12048BT | MLC | DW | B7G
Model Number Finish Edge Power Cutout

NO CUTOUT


QR No cutout

POWER CUTOUTS WHEN USED WITH BEAM BASES ONLY (Page 563)


B7G Center




B7H Left side




B7J Right side




B7K Centered in left side




B7L Centered in right side



B7M 2 cutouts in left side



B7N 2 cutouts in right side




B7H Left side

B7J Right side



B7K Centered in left side

B7L Centered in right side



B7M 2 cutouts in left side

B7N 2 cutouts in right side



Note: For a tapered top the left side location is at the narrow end.



Meeting Room planning guide

POWER CUTOUT LOCATIONS

To order, add location code(s) to model number.


Example: CT1-36-4G | MHM | EH | QV
Model Number Finish Edge Power Cutout

NO CUTOUT



QR No cutout

POWER CUTOUTS BETWEEN BASES


QS Between 1st Base and 2nd Base



QT Between 2nd Base and 3rd Base







QU Between 3rd Base and 4th Base






POWER CUTOUTS OVER BASES



QV Over 1st Base




QW Over 2nd Base



QX Over 3rd Base



QY Over 4th Base





Meeting Room planning guide

POWER SUPPLY AND BASE MATRIX

The Power Supplies can be used centered over select bases or between bases.

When ordering power supply **centered over base(s)**, refer to matrix for applicability.

Y = Power supply will work over this base

R = Power supply will work if **ROTATED** to run with base. Conference top must indicate **ROTATED** power supply

X = Power supply will not work over base

Description	Model No.	PS-37 PS-38	PSH-16PP	PS-43	PS-66 PS-67 PS-68	PS-69	PS-70 PS-99	PS-71
Curved	CB-A	X	X	X	X	X	X	X
Half Round	CBD-B	X	R	X	Y	R	R	X
Half Round	CB-B	X	Y	X	Y	R	R	X
Curved	CB-C	X	X	X	X	X	X	X
Panel	CB-D	X	X	X	X	X	X	X
Ellipse	CB-24EB	X	X	X	X	X	X	X
Cylinder	CB-F	X	Y	Y	Y	Y	Y	Y
Cylinder	CBH-F	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-F	Y	Y	Y	Y	Y	Y	Y
Duncan Phyfe	CB-L	X	X	X	X	X	X	X
Cylinder	CB-M	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-M	Y	Y	Y	Y	Y	Y	Y
Cross	CB-Q	X	X	X	X	X	X	X
Cross	CBU-Q	X	X	X	X	X	X	X
Cylinder	CB-R	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-R	Y	Y	Y	Y	Y	Y	Y
Panel	CB-S	X	X	X	X	X	X	X
Panel	CBD-S	X	X	X	X	X	X	X
Queen Anne	CB-T	X	X	X	X	X	X	X
Panel	CB-U	X	X	X	X	X	X	X
Panel	CBD-U	X	X	X	X	X	X	X
Panel	CB-2V	X	X	X	X	X	X	X
Panel	CB-Y	X	X	X	X	X	X	X
Panel	CBD-Y	X	X	X	X	X	X	X
Column	CB-03	X	R	X	Y	R	R	X
Column	CBH-03	R	Y	Y	Y	Y	Y	Y
Column (Square)	CB-04	X	Y	Y	Y	Y	Y	Y
Column (Square)	CBH-04	Y	Y	Y	Y	Y	Y	Y
Column (Square)	CBU-04	Y	Y	Y	Y	Y	Y	Y
Column	CB-05	X	R	X	Y	R	R	X
Column	CBH-05	R	Y	Y	Y	Y	Y	Y
Column (Square)	CB-06	X	Y	Y	Y	Y	Y	Y
Column (Square)	CBH-06	Y	Y	Y	Y	Y	Y	Y
Column (Square)	CBU-06	Y	Y	Y	Y	Y	Y	Y
Thick Panel	CB-12	X	Y	X	Y	R	R	X
Thick Panel	CBD-12	X	Y	X	Y	R	R	X



Meeting Room planning guide

POWER SUPPLY AND BASE MATRIX

The Power Supplies can be used centered over select bases or between bases.
When ordering power supply **centered over base(s)**, refer to matrix for applicability.

Y = Power supply will work over this base

R = Power supply will work if **ROTATED** to run with base. Conference top must indicate **ROTATED** power supply

X = Power supply will not work over base

Description	Model No.	PS-74 PS-75	PS-78	PS-111	PS-112	PS-81	PS-91 PS-91-BC	PS-92 PS-92-BC	PS-93 PS-93-BC	Grommet
Curved	CB-A	Y	X	X	X	X	Y	Y	Y	X
Half Round	CBD-B	Y	R	X	X	X	Y	Y	Y	Y
Half Round	CB-B	Y	R	R	R	X	Y	Y	Y	Y
Curved	CB-C	Y	X	X	X	X	Y	Y	Y	X
Panel	CB-D	X	X	X	X	X	X	X	X	X
Ellipse	CB-24EB	Y	X	X	X	X	Y	Y	Y	Y
Cylinder	CB-F	Y	Y	Y	X	X	Y	Y	Y	Y
Cylinder	CBH-F	Y	Y	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-F	Y	Y	Y	Y	Y	Y	Y	Y	Y
Duncan Phyfe	CB-L	X	X	X	X	X	X	X	X	X
Cylinder	CB-M	Y	Y	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-M	Y	Y	Y	Y	Y	Y	Y	Y	Y
Cross	CB-Q	Y	X	X	X	X	Y	Y	Y	Y
Cross	CBU-Q	Y	X	X	X	X	Y	Y	Y	Y
Cylinder	CB-R	Y	Y	Y	Y	Y	Y	Y	Y	Y
Cylinder	CBU-R	Y	Y	Y	Y	Y	Y	Y	Y	Y
Panel	CB-S	X	X	X	X	X	X	X	X	X
Panel	CBD-S	X	X	X	X	X	X	X	X	X
Queen Anne	CB-T	X	X	X	X	X	X	X	X	X
Panel	CB-U	X	X	X	X	X	X	X	X	X
Panel	CBD-U	X	X	X	X	X	X	X	X	X
Panel	CB-2V	X	X	X	X	X	X	X	X	X
Panel	CB-Y	X	X	X	X	X	X	X	X	X
Panel	CBD-Y	X	X	X	X	X	X	X	X	X
Column	CB-03	Y	R	R	R	X	Y	Y	Y	Y
Column	CBH-03	Y	Y	Y	R	R	Y	Y	Y	Y
Column (Square)	CB-04	Y	Y	Y	X	X	Y	Y	Y	Y
Column (Square)	CBH-04	Y	Y	Y	Y	Y	Y	Y	Y	Y
Column (Square)	CBU-04	Y	Y	Y	Y	Y	Y	Y	Y	Y
Column	CB-05	Y	R	R	R	X	Y	Y	Y	Y
Column	CBH-05	Y	Y	Y	R	R	Y	Y	Y	Y
Column (Square)	CB-06	Y	Y	Y	X	X	Y	Y	Y	Y
Column (Square)	CBH-06	Y	Y	Y	Y	Y	Y	Y	Y	Y
Column (Square)	CBU-06	Y	Y	Y	Y	Y	Y	Y	Y	Y
Thick Panel	CB-12	Y	R	R	R	X	Y	Y	Y	Y
Thick Panel	CBD-12	Y	R	R	R	X	Y	Y	Y	Y